

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191640807

Status:

Active

Overview:

Snap Plugs and Receptacles

Description:

Perma-Seal™ Male Snap Plug for 18-22 AWG Wire, Diameter 3.96mm, Mylar Tape Carrier



Series image - Reference only

Documents:	
Drawing (PDF)	Product Specification PS-19902-015-001 (PDF)
Product Specification PS-19902-011-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E152602
General	
Product Family	Quick Disconnects
Series	19164
Crimp Quality Equipment	Yes
Insulated	Partial
Overview	Snap Plugs and Receptacles
Product Name	Perma-Seal™
Type	Snap Plug
UPC	756054403310
Physical	
Barrel Type	Closed
Color - Resin	Red
Gender	Male
Glow-Wire Compliant	No
Insulation	NiAc™
Lock to Mating Part	None
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.018/g
Orientation	Straight
Packaging Type	Adhesive Tape on Reel
Tab Thickness	N/A
Tab Width	N/A
Temperature Range - Operating	-55°C to +125°C
Wire Insulation Diameter	5.97mm max.
Wire Size AWG	18, 20, 22
Electrical	
Voltage - Maximum	600V
Material Info	
Engineering Number	SA-269T
Reference - Drawing Numbers	
Product Specification	PS-19902-011-001, PS-19902-015-001
Sales Drawing	SD-19164-031

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19164 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION