

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0191640011](#)  
**Status:** **Active**  
**Overview:** [Splices](#)  
**Description:** Perma-Seal™ 3-Way Connector Assembly for 18-22 AWG Wire

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-19902-013-001 (PDF)</a>
<a href="#">Product Specification PS-19902-011-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Splices
Series	<a href="#">19164</a>
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	<a href="#">Splices</a>
Product Name	3 Way, Perma-Seal™
UPC	800753112995

**Physical**

Barrel Type	Closed
Color - Resin	Red
Insulation	NiAc™
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.838/g
Packaging Type	Bag
Temperature Range - Operating	-55°C to +125°C
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	5.46mm max.
Wire Size AWG	18, 20, 22

**Electrical**

Voltage - Maximum	600V
-------------------	------

**Material Info**

Engineering Number	SA-2YCX
--------------------	---------

**Reference - Drawing Numbers**

Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19164-051, SD-19204-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/01/2017 (12  
January 2017)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19164 Series](#)