

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0192030386**  
**Status:** **Active**  
**Overview:** Splices  
**Description:** Krimptite™ Temp-Term Butt Splice for 12-10 AWG Wire, 483°C (900° F), Loose Piece

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-19902-013-001 (PDF)</a>
<a href="#">Product Specification PS-19902-011-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Splices
Series	<u>19203</u>
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	<u>Splices</u>
Product Name	Krimptite™
UPC	822348424757

**Physical**

Barrel Type	Closed
Insulation	None
Material - Metal	Steel
Material - Plating Mating	Nickel
Material - Plating Termination	Nickel
Net Weight	1.630/g
Packaging Type	Bag
Temperature Range - Operating	483°C
Wire Insulation Diameter	5.80mm
Wire Size AWG	10, 12

**Material Info**

**Reference - Drawing Numbers**

Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19203-015



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/01/2017 (12  
January 2017)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

19203 Series