

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0039000120](#)
Status: **Active**
Overview: [Mini-Fit Jr. Power Connectors](#)
Description: [Mini-Fit® Male Crimp Terminal, Tin \(Sn\) Plated Brass Contact, 18-24 AWG, Reel](#)

Documents:

Drawing (PDF)	Product Specification TS-5556-002-001 (PDF)
Product Specification PS-5556-001 (PDF)	Packaging Specification PK-5558-001 (PDF)
Product Specification PS-5556-002-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	5558
Application	Power
Crimp Quality Equipment	Yes
Overview	Mini-Fit Jr. Power Connectors
Packaging Alternative	39-00-0121 (Loose)
Product Name	Mini-Fit®
UPC	800754395151

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.126/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	5558-S
--------------------	--------

Reference - Drawing Numbers

Packaging Specification	PK-5558-001
Product Specification	PS-5556-001, PS-5556-002-001, TS-5556-002-001
Sales Drawing	SD-5558-*S*



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[5558 Series](#)

Mates With

[5556 Mini-Fit® Crimp Terminal](#)

Use With

[5559 Mini-Fit Jr.™ Plug Housing](#), [30068 Mini-Fit® TPA Plug Housing](#), [42475 Mini-Fit® BMI Plug Housing](#)