
This document was generated on 09/12/2017

# PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** 0878335019
**Status:** Active
**Overview:** Milli-Grid™ Connector System
**Description:** Milli-Grid™ Header, Right Angle, Fully Shrouded, Lead-Free, 50 Circuits, Gold (Au) Flash Plating, without PCB Locator, without Locking Window, Center Polarization Slot, Tube



*Series image - Reference only*

**Documents:**

3D Model
Drawing (PDF)
Product Specification PS-87831-027-001 (PDF)
Packaging Specification PK-87831-001-001 (PDF)
RoHS Certificate of Compliance (PDF)

**Agency Certification**

| | |
|---|---|
| CSA | LR19980 |

**General**

| | |
|---|---|
| Product Family | PCB Headers |
| Series | 87833 |
| Application | Signal, Wire-to-Board |
| Comments | Contact Molex for application in automotive industry |
| Overview | Milli-Grid™ Connector System |
| Product Name | Milli-Grid™ |
| UPC | 822348353088 |

**Physical**

| | |
|---|---|
| Breakaway | No |
| Circuits (Loaded) | 50 |
| Circuits (maximum) | 50 |
| Color - Resin | Black |
| Durability (mating cycles max) | 100 |
| First Mate / Last Break | No |
| Flammability | 94V-0 |
| Glow-Wire Compliant | No |
| Guide to Mating Part | No |
| Keying to Mating Part | None |
| Lock to Mating Part | None |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Tin |
| Material - Resin | Nylon |
| Net Weight | 2.577/g |
| Number of Rows | 2 |
| Orientation | Right Angle |
| PC Tail Length | 2.16mm |
| PCB Locator | No |
| PCB Retention | None |
| PCB Thickness - Recommended | 1.60mm |
| Packaging Type | Tube |
| Pitch - Mating Interface | 2.00mm |
| Pitch - Termination Interface | 2.00mm |
| Plating min - Mating | 0.051µm |
| Plating min - Termination | 1.905µm |
| Polarized to PCB | No |
| Shrouded | Fully |
| Stackable | No |
| Surface Mount Compatible (SMC) | Yes |
| Temperature Range - Operating | -55°C to +105°C |

**EU ELV**
**Not Relevant**

**EU RoHS**
**Compliant**

**China RoHS**

**REACH SVHC**
Not Contained Per - ED/30/2017 (7 July 2017)

**Halogen-Free Status**
**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email productcompliance@molex.com
Please visit the Contact Us section for any non-product compliance questions.

| | |
|---|---|
| China ROHS | Green Image |
| ELV | Not Relevant |
| RoHS Phthalates | Not Contained |

**Search Parts in this Series**
87833 Series

**Mates With**
Milli-Grid™ Vertical Through Hole Receptacle 79107 , 78787 , Milli-Grid™ Flex-to-Board Vertical Receptacle 79108 , Milli-Grid™ Vertical Surface Mount Receptacle 79109 , 78788 , Milli-Grid™ Crimp Housing 51110 , Milli-Grid™ Cable-to-Board Receptacle 87568

| | |
|---|---|
| Termination Interface: Style | Through Hole |
| **Electrical** | |
| Current - Maximum per Contact | 2.0A |
| Voltage - Maximum | 125V |
| **Material Info** | |
| **Reference - Drawing Numbers** | |
| Packaging Specification | PK-87831-001-001 |
| Product Specification | PS-87831-027-001 |
| Sales Drawing | SD-87833-0001-001 |

This document was generated on 09/12/2017

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**