

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0193240005](#)
Status: **Active**
Overview: [Metric Ring Terminals](#)
Description: Avikrimp™ Metric Ring Terminal for Stud Size 10 (M5), Insulated Barrel

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

UL E32244

General

Product Family Ring and Spade Terminals
 Series [19324](#)
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview [Metric Ring Terminals](#)
 Product Name Avikrimp™
 Type Ring
 UPC 887191290058

Physical

Barrel Type Closed - Brazed
 Flammability 94V-2
 Insulation Nylon (PA)
 Material - Metal Copper Alloy
 Material - Plating Mating Tin
 Net Weight 1.204/g
 Packaging Type Bag
 Stud Size M5
 Wire Size AWG N/A
 Wire Size mm² 0.50-1.00

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number AA1-822-M5

Reference - Drawing Numbers

Sales Drawing SD-19324-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
 -ED/01/2017 (12
 January 2017)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[19324 Series](#)