

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0397000402](#)
Status: **Active**
Overview: Eurostyle™ Terminal Blocks
Description: 5.00mm Pitch, Eurostyle™ Fixed-Mount Push-Button Terminal Block, 45° Modular Luminaire, 10A, 26-14 AWG, Light Gray, 2 Circuits

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Terminal Blocks
Series	39700
Application	Wire-to-Board
Component Type	Push-Button
Overview	Eurostyle™ Terminal Blocks
Product Name	ESE, Eurostyle™ Fixed Mount
Type	Euro Block
UPC	78172542216

Physical

Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Gray (Light)
Entry Angle	45° Angle
Lock to Mating Part	No
Material - Plating Termination	Tin
Material - Resin	Nylon
Number of Rows	1
Orientation	45° Angle
Panel Mount	Yes
Pitch - Mating Interface	5.00mm
Polarized to Mating Part	No
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	14, 16, 18, 20, 22, 24, 26

Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	300V

Material Info

Engineering Number	M240-00-1-02-M3
--------------------	-----------------

Reference - Drawing Numbers

Sales Drawing	SD-39700-004
---------------	--------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[39700 Series](#)