

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0643193216](#)
Status: **Active**
Overview: CMC and CMX Sealed, Hybrid, Modular Connectors
Description: .635mm, 1.50mm, CMC Receptacle, 32 Circuits, Right Wire Output, Blue Coding, Mat Sealed

Documents:

3D Model	Application Specification AS-64319-002-SP-001 (PDF)
Drawing (PDF)	Application Specification AS-98420-002-CH-001 (PDF)
Product Specification PS-64319-001-001 (PDF)	Application Specification AS-98420-002-FR-001 (PDF)
Product Specification PS-64319-002-001 (PDF)	Application Specification AS-98420-002-SP-001 (PDF)
Application Specification AS-64319-002-001 (PDF)	Packaging Specification PK-64319-001-001 (PDF)
Application Specification AS-64319-002-CH-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-64319-002-FR-001 (PDF)	

General

Product Family	Crimp Housings
Series	64319
Application	Power, Wire-to-Board
Application Tooling Part Link	63812-1100
Application Tooling Part Link	63824-1200
Comments	Current tested on a 5 terminals loaded connector, current for temperature increase of 40°C . Current max = 6.0A for 0.635mm Terminal (0.75mm ² wire) and 12.0A for 1.50mm Terminal (2.00mm ² wire)
More Detailed Tech Information	Sealed, high-density, modular connecting system for Power Train and Body Electronics applications in cars, trucks, busses
Overview	CMC and CMX Sealed, Hybrid, Modular Connectors
Product Name	CMC
UPC	883906131142

Physical

Circuits (maximum)	32
Circuits Detail	8 x 1.5mm & 24 x 0.635mm terminals
Color - Resin	Blue
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	29.426/g
Number of Rows	4
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	2.54mm, 3.70mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

Electrical



Series image - Reference only

EU ELV
Compliant

EU RoHS **China RoHS**

Compliant
REACH SVHC
Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free
Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
64319 Series

Use With
CMC CP Terminals [64322](#) , [64323](#). CMC Wire Cap [64319-1201](#). Sealing Plugs [64325-1010](#) , [64325-1023](#)

Current - Maximum per Contact 12.0A, 6.0A

Solder Process Data

Lead-free Process Capability N/A

Material Info

Reference - Drawing Numbers

Application Specification AS-64319-002-001, AS-64319-002-CH-001,
AS-64319-002-FR-001, AS-64319-002-SP-001,
AS-98420-002-CH-001, AS-98420-002-FR-001,
AS-98420-002-SP-001

Packaging Specification PK-64319-001-001

Product Specification PS-64319-001-001, PS-64319-002-001

Sales Drawing SD-64319-001

This document was generated on 08/03/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION