

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0834249059](#)
Status: **Active**
Overview: [Commercial Micro-D High-Density Connectors](#)
Description: [Commercial Micro-D, CMD-to-CMD, 25 Circuits, Female - Female, 1.83m Length](#)

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-83422-001 \(PDF\)](#)
[Product Specification PS-83421-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	83424
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Commercial Micro-D-to-Commerci
Overview	Commercial Micro-D High-Density Connectors
Product Name	Commercial Micro-D
UPC	756054247129

Physical

Cable Length	1.83m
Circuits (Loaded)	25
Gender	Female-Female
Lock to Mating Part	None
Material - Plating Termination	Tin
Net Weight	46.430/g
Packaging Type	Bag
Plating min - Mating	0.127µm
Plating min - Termination	1.270µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	.225mm (5.720") max.
Wire Size AWG	28
Wire/Cable Type	N/A

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-83422-001
Product Specification	PS-83421-001-001
Sales Drawing	SD-83424-006



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/108/2014 (17 Dec
2014)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Reviewed

Search Parts in this Series

[83424 Series](#)