

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0956223981](#)
Status: **Active**
Overview: Magnetic and Modular Jacks and Plugs
Description: Modular Jack, Right Angle, Through Hole, 8/8, Shielded, Tube

Documents:

| | |
|--|--|
| 3D Model | Test Summary STR-1424-001 (PDF) |
| Drawing (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-95622-001-001 (PDF) | Product Literature (PDF) |
| Test Summary STR-1162-001 (PDF) | |

Agency Certification

UL E107635

General

| | |
|-----------------------------|--|
| Product Family | Modular Jacks/Plugs |
| Series | 95622 |
| Comments | Reflow Capable, External Shield |
| Component Type | PCB Jack |
| Magnetic | No |
| Overview | Magnetic and Modular Jacks and Plugs |
| Performance Category | 3 |
| Power over Ethernet (PoE) | N/A |
| Product Literature Order No | 987650-8441 |
| Product Name | Modular Jack 8/8 |
| UPC | 800756963631 |

Physical

| | |
|--------------------------------|--------------------------------|
| Boot Color | N/A |
| Color - Resin | Black |
| Durability (mating cycles max) | 2500 |
| Flammability | 94V-0 |
| Inverted / Top Latch | No |
| Jack Height | 13.00mm |
| Keying to Mating Part | None |
| Lightpipes/LEDs | None |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Gold over Palladium Nickel |
| Material - Plating Termination | Tin |
| Material - Resin | High Temperature Thermoplastic |
| Net Weight | 5.034/g |
| Orientation | Right Angle (Side Entry) |
| PCB Locator | Yes |
| PCB Retention | Yes |
| PCB Thickness - Recommended | 1.57mm |
| Packaging Type | Tube |
| Pitch - Mating Interface | 1.02mm |
| Pitch - Termination Interface | 1.27mm |
| Plating min - Mating | 0.051µm, 0.600µm |
| Plating min - Termination | 1.905µm |
| Ports | 1 |
| Positions / Loaded Contacts | 8/8 |
| Surface Mount Compatible (SMC) | No |
| Temperature Range - Operating | -40°C to +85°C |
| Termination Interface: Style | Through Hole |
| Waterproof / Dustproof | No |
| Wire/Cable Type | N/A |

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

| | |
|-----------------|---------------|
| China ROHS | Green Image |
| ELV | Not Relevant |
| RoHS Phthalates | Not Contained |

Search Parts in this Series

[95622](#) Series

Mates With

[95043](#) Modular Plug, Short Body

Electrical

| | |
|-------------------------------|---------|
| Current - Maximum per Contact | 1.5A |
| Grounding to PCB | Yes |
| Grounding to Panel | None |
| Shielded | Yes |
| Voltage - Maximum | 125V DC |

Material Info**Reference - Drawing Numbers**

| | |
|-----------------------|----------------------------|
| Product Specification | PS-95622-001-001 |
| Sales Drawing | SD-95622-003 |
| Test Summary | STR-1162-001, STR-1424-001 |

This document was generated on 08/29/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION