

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0395140004](#)  
**Status:** **Active**  
**Overview:** Eurostyle™ Terminal Blocks  
**Description:** 3.81mm Pitch Eurostyle™ Horizontal Plug, with Retention Screws, 4 Circuits

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-39500-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-39514-001 (PDF)</a>
<a href="#">Product Specification PS-39500-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

UL E48521

**General**

Product Family	Terminal Blocks
Series	<a href="#">39514</a>
Application	N/A
Component Type	Plug
Overview	<a href="#">Eurostyle™ Terminal Blocks</a>
Product Name	ESE, Eurostyle™ Pluggable
Type	Euro Block
UPC	822350688918

**Physical**

Circuits (Loaded)	4
Entry Angle	Vertical
Lock to Mating Part	Yes
Number of Rows	1
Orientation	Horizontal
Panel Mount	No
Pitch - Mating Interface	3.81mm
Pitch - Termination Interface	3.81mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	16, 18, 20, 22, 24
Wire Size mm²	0.20-1.31


**Electrical**

Current - Maximum per Contact	8.0A
Voltage - Maximum	300V

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-39500-001, PK-39514-001
Product Specification	PS-39500-001-001
Sales Drawing	SD-39514-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[39514 Series](#)

**Mates With**

Most 3.81mm Pitch Industry Standard PCB Headers, [39515 Vertical PCB Header with Threaded Retention Inserts](#), [39516 Horizontal PCB Header with Threaded Retention Inserts](#)