

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0433740001](#)
Status: **Active**
Overview: [Sabre™ Power Connector](#)
Description: Sabre™ Crimp Terminal, Female, 14-16 AWG, 0.79mm max. Insulation Diameter, Reel Packaged, Tin (Sn) Plated Brass Contact without TPA



Series image - Reference only

Documents:

Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-43374-001-001 (PDF)	Product Literature (PDF)

General	
Product Family	Crimp Terminals
Series	43374
Application	Power
Comments	Terminal mates to 3.18mm wide x 0.51mm thick flat blade PC tab
Crimp Quality Equipment	Yes
Overview	Sabre™ Power Connector
Product Literature Order No	987650-5662
Product Name	Sabre™
UPC	800753851139

Physical	
Durability (mating cycles max)	25
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.312/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.79mm max.
Wire Size AWG	14, 16
Wire Size mm²	N/A

Electrical	
Current - Maximum per Contact	18.0A
Voltage - Maximum	600V

Solder Process Data	
Lead-freeProcess Capability	N/A

Material Info

Reference - Drawing Numbers	
Product Specification	PS-43374-001-001
Sales Drawing	SD-43374-0001

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[43374](#) Series

Mates With

[43178](#) Male Crimp Terminals

Use With

[44441](#) Receptacle Housings