

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5023820670](#)
Status: **Active**
Overview: [CLIK-Mate Wire-to-Board Connectors](#)
Description: 1.25mm Pitch CLIK-Mate Wire-to-Board PCB Receptacle, Single Row, Vertical, Tin Plating, 6 Circuits

Documents:

| | |
|---|---|
| 3D Model (PDF) | Application Specification AS-502380-002-001 (PDF) |
| 3D Model | Packaging Specification SPK-502382-001-001 (PDF) |
| Drawing (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-502382-001-001 (PDF) | |

Agency Certification

UL E29179

General

| | |
|----------------|--|
| Product Family | PCB Receptacles |
| Series | 502382 |
| Application | Signal, Wire-to-Board |
| Overview | CLIK-Mate Wire-to-Board Connectors |
| Product Name | CLIK-Mate |
| UPC | 822350895231 |

Physical

| | |
|--------------------------------|--------------------------------|
| Circuits (Loaded) | 6 |
| Circuits (maximum) | 6 |
| Color - Resin | Natural |
| Durability (mating cycles max) | 30 |
| Glow-Wire Capable | No |
| Guide to Mating Part | Yes |
| Keying to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Mated Height | 7.80mm |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | High Temperature Thermoplastic |
| Net Weight | 302.001/mg |
| Number of Rows | 1 |
| Orientation | Vertical |
| PCB Locator | No |
| PCB Retention | Yes |
| Packaging Type | Embossed Tape on Reel |
| Pitch - Mating Interface | 1.25mm |
| Pitch - Termination Interface | 1.25mm |
| Plating min - Mating | 1.016µm |
| Plating min - Termination | 1.016µm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | No |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |
| Termination Interface: Style | Surface Mount |

Electrical

| | |
|-------------------------------|-----------------|
| Current - Maximum per Contact | 1.0A |
| Voltage - Maximum | 50V AC (RMS)/DC |

Material Info



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[502382](#) Series

Mates With

[502380](#) CLIK-Mate Housing

Reference - Drawing Numbers

Application Specification

AS-502380-002-001

Packaging Specification

SPK-502382-001-001

Product Specification

PS-502382-001-001

Sales Drawing

SD-502382-001, SD-502382-003

This document was generated on 12/20/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION