


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5031543290](#)
Status: **Active**
Overview: [CLIK-Mate Wire-to-Board Connectors](#)
Description: 1.50mm Pitch, CLIK-Mate PCB Receptacle, Dual Row, Surface Mount, Vertical, Tin Plating, Positive Lock, 32 Circuits, Natural

Documents:

3D Model	Product Specification 5031491000-PS-000 (PDF)
Drawing (PDF)	Application Specification AS-503149-001-001 (PDF)
3D Model (PDF)	Packaging Specification SPK-503154-001-001 (PDF)
Product Specification 5031490000-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)



Series image - Reference only

Agency Certification

UL E29179

General

Product Family	PCB Receptacles
Series	503154
Application	Signal, Wire-to-Board
Overview	CLIK-Mate Wire-to-Board Connectors
Product Name	CLIK-Mate
UPC	884982022867

Physical

Circuits (Loaded)	32
Circuits (maximum)	32
Color - Resin	Beige
Durability (mating cycles max)	30
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Mated Height	11.20mm
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	2388.001/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.20mm, 1.70mm
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.50mm
Pitch - Termination Interface	1.50mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	100V

Material Info

Reference - Drawing Numbers

Application Specification	AS-503149-001-001
---------------------------	-------------------

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[503154 Series](#)

Mates With

[503149 Crimp Housing](#)

Packaging Specification
Product Specification
Sales Drawing

SPK-503154-001-001
5031490000-PS-000, 5031491000-PS-000
5031540000-SD-000

This document was generated on 03/10/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION