

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5037630491](#)
Status: **Active**
Overview: [Pico-Lock Connector System](#)
Description: 1.00mm Pitch, Pico-Lock PCB Header, Single Row, Right-Angle, Surface Mount, Gold over Nickel Plating, Positive Lock, 4 Circuits, Tape and Reel

Documents:

3D Model	Application Specification AS-503764-002-001 (PDF)
3D Model (PDF)	Packaging Specification SPK-503763-001-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-503764-001-001 (PDF)	Product Literature (PDF)
Application Specification AS-503764-001-001 (PDF)	

Agency Certification

UL E29179

General

Product Family	PCB Headers
Series	503763
3D Viewer	Yes
Application	Signal, Wire-to-Board
CURRENT-MAX-NUMERIC	1.5
Overview	Pico-Lock Connector System
PITCH-MATING-NUMERIC	1.00
Product Literature Order No	987650-9061
Product Name	Pico-Lock
UPC	887191353838

Physical

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	SC-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	N/A
Lock to Mating Part	Yes
Mated Height	1.50mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Resin	High Temperature Thermoplastic
Net Weight	76.240/mg
Number of Rows	1
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	0.100µm
Polarized to Mating Part	Yes
Shrouded	Yes
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[503763](#) Series

Mates With

Pico-Lock Crimp Housing [503764](#)
Pico-Lock Cable Assembly [15131](#)

Electrical

Current - Maximum per Contact
Voltage - Maximum

1.5A
150V AC (RMS)/DC

Material Info**Reference - Drawing Numbers**

Application Specification
Packaging Specification
Product Specification
Sales Drawing

AS-503764-001-001, AS-503764-002-001
SPK-503763-001-001
PS-503764-001-001
SD-503763-001-001, SD-503763-002-001,
SD-503764-001-001

This document was generated on 12/12/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION