


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [5051100992](#)  
**Status:** **Active**  
**Overview:** Easy-On FFC FPC Connectors  
**Description:** Easy-On FFC/FPC Connector, 0.50mm Pitch, FD19 Series, Right-Angle, Bottom Contact, 1.90mm Height, 9 Circuits, Gold over Nickel Plating

**Documents:**

|                                 |  |
|---------------------------------|--|
| <a href="#">Drawing (PDF)</a>   | <a href="#">Product Guide (PDF)</a>                  |
| <a href="#">3D Model</a>        | <a href="#">RoHS Certificate of Compliance (PDF)</a> |
| <a href="#">3D Model (PDF)</a>  | <a href="#">Reference Guide (PDF)</a>                |
| <a href="#">Datasheet (PDF)</a> |  |



**General**

|                |  |
|----------------|--|
| Product Family | FFC/FPC Connectors                         |
| Series         | <a href="#">505110</a>                     |
| Comments       | Black Actuator, Black Actuator             |
| Overview       | <a href="#">Easy-On FFC FPC Connectors</a> |
| Product Name   | Easy-On                                    |
| Series Name    | FD19                                       |
| UPC            | 889056255837                               |

**Physical**

|                                |                        |
|--------------------------------|------------------------|
| Actuator Type                  | Flip                   |
| Circuits (Loaded)              | 9                      |
| Color - Resin                  | Beige                  |
| Contact Position               | Bottom                 |
| Durability (mating cycles max) | 20                     |
| Mated Height                   | 1.90mm                 |
| Material - Metal               | Phosphor Bronze        |
| Material - Plating Mating      | Gold over Nickel       |
| Material - Plating Termination | Gold over Nickel       |
| Material - Resin               | Liquid Crystal Polymer |
| Net Weight                     | 106.480/mg             |
| Number of Rows                 | 1                      |
| Orientation                    | Right Angle            |
| PCB Locator                    | No                     |
| PCB Mounting                   | Surface Mount          |
| PCB Retention                  | Yes                    |
| Packaging Type                 | Embossed Tape on Reel  |
| Pitch - Mating Interface       | 0.50mm                 |
| Pitch - Termination Interface  | 0.50mm                 |
| Plating min - Mating           | 0.051µm                |
| Plating min - Termination      | 0.051µm                |
| Polarized to PCB               | Yes                    |
| Stackable                      | No                     |
| Temperature Range - Operating  | -40° to +105°C         |
| Wire/Cable Type                | FFC/FPC                |

**Electrical**

|                               |                 |
|-------------------------------|-----------------|
| Current - Maximum per Contact | 0.5A            |
| Voltage - Maximum             | 50V AC (RMS)/DC |

**Material Info**

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/71/2019 (16 July  
2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[505110 Series](#)

**Mates With**

Premo-Flex FFC Cable [15020](#) , [15018](#)

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**