

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0797580002](#)
Status: **Active**
Overview: [Pre-Crimped Leads](#)
Description: Pre-Crimped Lead Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female Tin Plated, 150mm, 20 AWG

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	79758
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Micro-Fit 3.0™ Crimp Terminals
Overview	Pre-Crimped Leads
Product Name	Micro-Fit 3.0™
UPC	884982052659

Physical

Cable Length	0.15m
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.045/g
Packaging Type	Bag
Single Ended	No
Wire Size AWG	20
Wire/Cable Type	UL 1061

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-797580001
---------------	--------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[79758](#) Series

Mates With

[43031](#) Micro-Fit 3.0 Male Crimp Terminals

Use With

[43645](#) , [43025](#) Micro-Fit 3.0 Receptacle Housings, [44133](#) , [44300](#) Micro-Fit BMI Panel Mount Housings