

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0192030182](#)  
**Status:** **Active**  
**Overview:** [High-Temperature Temp Terms Terminals and Splices](#)  
**Description:** VersaKrimp™ Temp-Term Ring Tongue Terminal for 10 to 12 AWG Wire, Stud Size 1/4" (M6)

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-19902-013-001 (PDF)</a>
<a href="#">Product Specification PS-19902-011-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

UL E32244

**General**

Product Family	Ring and Spade Terminals
Series	<a href="#">19203</a>
Comments	650° F (343° C)
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	<a href="#">High-Temperature Temp Terms Terminals and Splices</a>
Product Name	Temp-Terms, VersaKrimp™
Type	Ring
UPC	800755060072

**Physical**

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	1.997/g
Packaging Type	Bag
Stud Size	1/4" (M6)
Wire Size AWG	10, 12
Wire Size mm²	4.00-6.00

**Material Info**

Engineering Number C-T-330-14

**Reference - Drawing Numbers**

Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	CTCD30101



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/01/2017 (12  
January 2017)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19203 Series](#)