

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0387068010](#)  
**Status:** **Active**  
**Overview:**  
**Description:** 8.26mm Pitch Beau™ PCB Terminal Strip, without Mounting Ends, Dual Level Terminal Block, 10 Circuits

**General**

Product Family	Terminal Blocks
Series	<a href="#">38706</a>
Application	N/A
Component Type	One Piece
Overview	beau_barrier_strips
Product Name	Fixed Mount Barrier
Type	Barrier Strip
UPC	883906405403

**Physical**

Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Entry Angle	N/A
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polysulfone
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.56mm
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Panel Mount	No
Pitch - Mating Interface	8.26mm
Pitch - Termination Interface	8.26mm
Polarized to Mating Part	N/A
Shrouded	Dual-Barrier
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	160°C
Termination Interface: Style	Through Hole
Wire Size AWG	12, 14, 16, 18, 20, 22

**Electrical**

Current - Maximum per Contact	20.0A
Voltage - Maximum	300V

**Material Info**

Old Part Number	70D10-RC
-----------------	----------

**Reference - Drawing Numbers**

Sales Drawing	SD-38706-001
---------------	--------------

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

**Search Parts in this Series**

[38706 Series](#)