


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1712241011](#)  
**Status:** **Active**  
**Overview:** High-Speed Pluggable I/O Solutions  
**Description:** zSFP+® Stacked Ganged Assembly with Metal Spring Fingers, 2-by-1 With 4 Light Pipes, 40 Circuits

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-170071-0002-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-170071-002 (PDF)</a>
<a href="#">Product Specification PS-170071-0001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification TS-170071-0001-001 (PDF)</a>	



**Agency Certification**

UL E29179

**General**

Product Family	I/O Connectors
Series	<a href="#">171224</a>
Application	Module-to-Board
Component Type	Receptacle
Overview	<a href="#">High-Speed Pluggable I/O Solutions</a>
Product Name	zSFP+®
Type	N/A
UPC	884982822924

**Physical**

Circuits (Loaded)	40
Color - Resin	Black
Durability (mating cycles max)	100
Flammability	94V-0
Gender	Female
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	27.867/g
Number of Rows	2
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.36mm
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	2
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Through Hole - Compliant Pin

**Electrical**

Current - Maximum per Contact 0.5A

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/30/2017 (7 July  
2017)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[171224 Series](#)

Shield Type	N/A
Shielded	Yes
Voltage - Maximum	30V AC

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info****Reference - Drawing Numbers**

Application Specification	AS-170071-0002-001
Electrical Model Document	EE-170071-0001
Packaging Specification	PK-170071-002
Product Specification	PS-170071-0001, TS-170071-0001-001
S-Parameter Model	SP-170426-1000
Sales Drawing	SD-171224-0002

This document was generated on 09/22/2017

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**