



Part Number : 1053860004
Product Description : Reinforced, Anti-Snag Spring Clip, 1.00mm Width, 1.0µm Gold (Au) Plating, 0.40mm - 0.80mm Working Range (Height)
Series Number : 105386
Status : Obsolete
Product Category : Connector Accessories



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Connector Accessories
Series	105386
Description	Reinforced, Anti-Snag Spring Clip, 1.00mm Width, 1.0µm Gold (Au) Plating, 0.40mm - 0.80mm Working Range (Height)
Component Type	Clip
Product Name	Spring Clip
UPC	889056283656

Electrical

Current - Maximum per Contact	1.5A
-------------------------------	------

Physical

Circuits (Loaded)	1
Circuits (maximum)	1
Material - Metal	Stainless Steel
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.023/g
Packaging Type	Embossed Tape on Reel
Plating min - Mating	1.016µm
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Solder