



Part Number : [1060597900](#)

Product Description : Optical Industrial Plug Assembly, Metal Body, Outdoor Cable, LC, Singlemode, Male

Series Number : 106059

Status : Not Recommended For New Design

Product Category : Fiber Optic Connectors



Documents and Resources

Drawings

[1060597900_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

Part Details

General

Status	Not Recommended For New Design
Category	Fiber Optic Connectors
Series	106059
Description	Optical Industrial Plug Assembly, Metal Body, Outdoor Cable, LC, Singlemode, Male
Mode	Singlemode
Product Name	LC
UPC	883906155964

Physical

Angled Physical Contact (APC)	No
Boot Color	N/A
Boot Type	N/A
Cable Size	8.00mm max.
Color - Resin	N/A
Ferrule Hole Size	125.5µm
Ferrule Material	Ceramic
Gender	Plug
Material - Housing	PBT
Mounting Style	Adhesive
Net Weight	116.210/g
Ports	2
Wire/Cable Type	N/A