



Part Number : [1064134020](#)

Product Description : OptoUSB USB 3.1 Type A
Active Optical Cable, 50/125µm, 5.00mm, Multimode
20.0m Length

Series Number : 106413

Status : Active

Product Category : Fiber Optic Cable Assemblies



Documents and Resources

Drawings

[1064134020_sd.pdf](#)

Specifications

[1064134001-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2020)4578-DC (25 June 2020)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Fiber Optic Cable Assemblies
Series	106413
Description	OptoUSB USB 3.1 Type A Active Optical Cable, 50/125µm, 5.00mm, Multimode 20.0m Length
Connector to Connector	USB Type A-to-A
Mode	Multimode
Product Name	OptoUSB,USB 3.1
UPC	191128850087

Physical

Boot Type	Straight
Cable Length	20.0m
Cable Size	5.00mm
Fiber (Core/Cladding)	50/125µm
Net Weight	0.001/g
Single Ended	No
Wire/Cable Type	Hybrid – Optical/Copper