

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

106415-2010

Status:

Active

Overview:

Fiber Optic Product Families

Description:

iPASS+™ High Density AOC Assembly (iPass+-to-iPass+), Multimode, 50/125µm, Cable Diameter 3.00mm, Cable Length 10.00m

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Fiber Optic Assemblies
Series	106415
Connector to Connector	iPass+™-to-iPass+™
Mode	Multimode
Overview	Fiber Optic Product Families
Product Name	AOC, iPass+™
UPC	887191172736
Physical	
Cable Length	10.0m
Cable Size	3.00mm
Fiber (Core/Cladding)	50/125µm
Single Ended	No
Wire/Cable Type	Fiber Optic, Round
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-106415-2001



image - Reference only

Series

EU RoHS

Compliance Status

Not Reviewed

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

106415Series

Mates With

External iPass+ Integrated Connector [76866](#)

, Internal iPass+ Integrated Connector [76867](#)

Use With

Mini SAS HD 2.1 4X Cable Assembly [111068](#) , [111077](#) , Internal Cable Assemblies [100190](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION