



Part Number : [1110150201](#)
Product Description : HSAutoLink Cable Assembly,
USCAR/USB TYPE A Receptacle-to-MINI-B Plug, 1.00m
Length, Polarization B
Series Number : 111015
Status : Active
Product Category : Power and Signal Cable
Assemblies



Documents and Resources

Drawings
[1110150201 sd.pdf](#)
[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications
[PS-68800-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Duty-To-Declare
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

- Compliance Statements
- EU RoHS
 - REACH SVHC
 - Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	111015
Description	HSAutoLink Cable Assembly, USCAR/USB TYPE A Receptacle-to-MINI-B Plug, 1.00m Length, Polarization B
Application	Automotive
Assembly Configuration	Dual Ended Connectors
Comments	USCAR-30 Compliant
Connector to Connector	USB Type A-to-Mini-B
Product Name	HSAutoLink USCAR/USB
UPC	883906510091

Physical

Cable Length	1.0m
Circuits (Loaded)	N/A
Gender	Male-Female
Lock to Mating Part	Yes
Net Weight	61.756/g
Number of Rows	1
Single Ended	No
Wire/Cable Type	Round

Mates With / Use With

Mates with Part(s)

Description	Part Number
HSAutoLink Right-Angle Headers	<u>49616</u>