



Part Number : [1110192010](#)
Product Description : HSAutoLink Cable Assembly,
LVDS MINI-B Plug-to-MINI-B Inline Receptacle, 0.50m
Length, Polarization A-to-A
Series Number : 111019
Status : Active
Product Category : Power and Signal Cable
Assemblies



Documents & Resources

Drawings

- [1110192010 sd.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	111019
Description	HSAutoLink Cable Assembly, LVDS MINI-B Plug-to-MINI-B Inline Receptacle, 0.50m Length, Polarization A-to-A
Application	Automotive
Assembly Configuration	Dual Ended Connectors
Connector to Connector	STP 100/PG Mini-B-to-Mini-B
Product Name	HSAutoLink LVDS
UPC	883906510268

Physical

Cable Length	0.50m
Circuits (Loaded)	N/A
Gender	Male-Female
Lock to Mating Part	Yes
Net Weight	32.100/g
Number of Rows	1
Single Ended	No
Wire/Cable Type	Round

Mates With / Use With

Mates with Part(s)

Description	Part Number
HSAutoLink Right-Angle Headers	<u>49616</u>