



Part Number : [1110401504](#)
Product Description : QSFP+-to-QSFP+ Cable
Assembly, 30 AWG, 5.0m Length
Series Number : 111040
Status : Active
Product Category : High-Speed I/O Cable
Assemblies



Documents & Resources

Drawings

[1110401504_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

Part Details

General

Status	Active
Category	High-Speed I/O Cable Assemblies
Series	111040
Description	QSFP+-to-QSFP+ Cable Assembly, 30 AWG, 5.0m Length
Assembly Configuration	Dual Ended Connectors
Connector to Connector	QSFP+-to-QSFP+
Product Name	QSFP Plus,QSFP+
Type	Pluggable
UPC	884982003187

Agency

UL	E72548
----	--------

Electrical

Data Rate	10.0 Gbps
Impedance	100Ω

Physical

Cable Bundling	None
Cable Length	5.0m
Circuits (Loaded)	MSA
Gender	Plug
Lock to Mating Part	Yes
Net Weight	244.000/g
Packaging Type	Bag
Release Style	Pull Tab
Single Ended	No
Wire/Cable Type	Round

Wire Size (AWG)	30
-----------------	----

Mates With / Use With

Mates with Part(s)

Description	Part Number
iPass I/O Right-Angle Surface Mount Receptacles	<u>75586</u>

Use with Part(s)

Description	Part Number
QSFP+ Cage Assemblies, Light Pipes, and Heat Sinks	<u>74750</u>
QSFP+ 1x3 Ganged Cage Assemblies and Heat Sink Clips	<u>74768</u>
QSFP+ Ganged Cages and Light Pipe Assemblies	<u>74769</u>