



Part Number : [134250001](#)
Product Description : Alien Handheld Android RFID
Reader Kit, 902-928 MHz, for USA
Series Number : 13425
Status : Active
Product Category : Asset Tracking
Engineering Part Number : ALR-H460



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Asset Tracking
Series	13425
Description	Alien Handheld Android RFID Reader Kit, 902-928 MHz, for USA
Comments	Memory Expansion: MicroSD (128 GB Max)
Component Type	Handheld RFID Reader
Kit Components	Handheld Reader, Pistol Grip, Charging Dock, USB Cable, Power Adapter
Kit Option	Reader Kit
Market	Some Latin American Countries, USA
Product Name	Alien
RFID Standard	EPC C1 Gen 2,ISO 18000-6c
Type	Handheld
UPC	193264422401

Electrical

Frequency	902-928 MHz
Max Conductive RF Power (dBm)	31.6
Power Source	Battery

Physical

Additional Readers Supported	None
Antennas	1 dBiL / 4 dBiC (Circular)
Communications	OTG (Direct attach to H460), USB 2.0 Type C
Dimensions	178.00 x 86.00 x 146.00mm, with pistol grip
Memory	2 GB RAM,16 GB Flash
Operating System	Android 6.0

Packaging Type	Carton
Temperature Range - Operating	-10° to +50°C

This document was generated on Mar 24, 2026