



Part Number : [135090001](#)

Product Description : Button RFID Tag, 24.9mm Read Range, 14.50mm Diameter Footprint, For Non-Metal Surfaces, Adhesive Attachment

Series Number : 13509

Status : Active

Product Category : Asset Tracking

Documents and Resources

Drawings

[135090001_sd.pdf](#)

Specifications

[135090001-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Reviewed
China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[CE - Declaration of Conformity](#)

Part Details

General

Status	Active
Category	Asset Tracking
Series	13509
Description	Button RFID Tag, 24.9mm Read Range, 14.50mm Diameter Footprint, For Non-Metal Surfaces, Adhesive Attachment
Component Type	RFID Tag
Product Name	RFID Solutions
Type	For Non-Metal Surfaces
UPC	196823153280

Electrical

Frequency	13.56 MHz
-----------	-----------

Physical

Dimensions	14.50mm dia x 3.00mm Thickness
Mounting Style	Adhesive
Outer Diameter	14.50mm
Packaging Type	Bag
Read Range	24.9mm
Thickness	3.00mm