Part Number : 135250001
Product Description : Button RFID Tag, 30.0mm Read Range, 34.00mm Diameter Footprint, For Metal Surfaces, Screw or Adhesive Attachment
Series Number : 13525
Status : Active
Product Category : Asset Tracking



Documents and Resources

Drawings

135250001_sd.pdf

Specifications

135250001-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Asset Tracking
Series	13525
Description	Button RFID Tag, 30.0mm Read Range, 34.00mm Diameter Footprint, For Metal Surfaces, Screw or Adhesive Attachment
Component Type	RFID Tag
Product Name	RFID Solutions
Type	For Metal Surfaces
UPC	196823496134

Electrical

Frequency	13.56 MHz

Physical

Dimensions	34.00mm dia x 6.00mm Thickness
Mounting Style	Adhesive, Screws
Outer Diameter	34.00mm
Packaging Type	Bag
Read Range	30.0mm
Thickness	6.00mm