



Part Number : [1510492601](#)
Product Description : CP-6.5 Receptacle Housing,
6.50mm Pitch, Dual Row, Polarized, Positive Lock, 6
Circuits, Blue
Series Number : 151049
Status : Active
Product Category : Connector Housings



Documents & Resources

Drawings

[1510492601_sd.pdf](#)
[PK-151049-0001-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications

[PS-151048-0001-001.pdf](#)
[1510480001-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	151049
Description	CP-6.5 Receptacle Housing, 6.50mm Pitch, Dual Row, Polarized, Positive Lock, 6 Circuits, Blue
Application	Power, Wire-to-Board
Comments	See Product Specification for maximum current rating by circuit size and wire AWG
Product Name	CP-6.5
UPC	889056065900

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	6
Color - Resin	Blue
Flammability	94V-0

Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBTP
Net Weight	2.653/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.50mm
Pitch - Termination Interface	6.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
CP-6.5 Header, 6.50mm Pitch, Dual Row, Vertical, Polarized, Positive Lock, Tray Packaging, Glow-Wire Capable, 6 Circuits, Blue	<u>1510481601</u>

Use with Part(s)

Description	Part Number
CP-6.5 Wire-to-Board Crimp Terminal, Female, 22-16 AWG, Reel	<u>505978000</u>
CP-6.5 Wire-to-Board Crimp Terminal, Female, 26-20 AWG, Reel	<u>505988000</u>
CP-6.5 Terminal Position Assurance (TPA) Retainer, 3 Circuits	<u>511430305</u>