



Part Number : [1600280014](#)
Product Description : stAK50h Hybrid Receptacle,
32 Circuits, Key 4, Rib Option A, Purple, Bag
Series Number : 160028
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

[1600280014_sd.pdf](#)
[PK-31302-266-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications

[1600140001-AS-CH-000.pdf](#)
[AS-160014-001-001.pdf](#)
[1600140001-000.pdf](#)
[1600140000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	160028
Description	stAK50h Hybrid Receptacle, 32 Circuits, Key 4, Rib Option A, Purple, Bag
Application	Automotive, Wire-to-Board
Component Type	Housing
Product Name	stAK50h
UPC	193264073061

Physical

Circuits (maximum)	32
Color - Resin	Purple
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS
Net Weight	5.401/g
Number of Rows	5

Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm, 4.00mm
Pitch - Termination Interface	2.00mm, 4.00mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +105°C LV-214, -40° to +85°C GMW3191 June2012

Mates With / Use With

Mates with Part(s)

Description	Part Number
stAK50h Vertical Hybrid Header, 32 Circuits, Key 4, Purple, Tube	<u>2005010324</u>
stAK50h Right-Angle Hybrid Header, 32 Circuits, Key 4, Purple, Tube	<u>2005020324</u>

Use with Part(s)

Description	Part Number
TAK50 Unsealed Receptacle Terminals	<u>200096</u>
Use With	Aptiv OCS 1.20mm Terminal or JST MSA 1.20mm Terminal