Part Number : 1600813004
Product Description : MX150 Hybrid Mat-Sealed Male Connector Assembly, Dual Row, 9 Circuits, Keying Option D, Stone Gray
Series Number : 160081
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

1600813004_sd.pdf

PK-31300-635-001.pdf

PK-31300-903-001.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

1601110001-AS-000.pdf

1600760001-PS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	160081
Description	MX150 Hybrid Mat-Sealed Male Connector Assembly, Dual Row, 9 Circuits, Keying Option D, Stone Gray
Application	Power, Wire-to-Wire, Automotive
Product Name	MX150
UPC	193264496211

Physical

Circuits (maximum)	9
Color - Resin	Stone Gray
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	21.515/g
Number of Rows	2
Packaging Type	Bag

Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarization	D
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Use with Part(s)

Description	Part Number
MX150 Male Terminals	33000
MX150 Male Terminals	33011
Use With	Industry Standard Terminal 2.80mm