



Part Number : [1707290001](#)
Product Description : iPass+ zHD Vertical Internal Connector Assembly, 1x1, Through Hole, 0.76µm Gold (Au) Plating
Series Number : 170729
Status : Active
Product Category : High-Speed I/O Connectors



Documents & Resources

Drawings

[1707290001_sd.pdf](#)
[PK-76867-002-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)
[SYM-170729-0001-001.zip](#)
[EE-170729-0001-001.pdf](#)
[SI-170729-0001-001.pdf](#)
[SP-170729-0001-001.zip](#)

Specifications

[1707290002-000.pdf](#)
[AS-170729-0001-001.pdf](#)
[AS-76867-002-001.pdf](#)
[PS-170729-001-001.pdf](#)
[1707290001-000.pdf](#)
[TS-170729-9906-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	

	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	High-Speed I/O Connectors
Series	170729
Description	iPass+ zHD Vertical Internal Connector Assembly, 1x1, Through Hole, 0.76µm Gold (Au) Plating
Application	Wire-to-Board
Component Type	Internal Receptacle
Product Name	iPass+,zHD
Type	Pluggable
UPC	887191187877

Agency

CSA	LR19980
UL	E107635

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	48V AC (RMS) / 67V DC

Physical

Circuits (Loaded)	36
Circuits (maximum)	36
Color - Resin	Black
Durability (mating cycles max)	50
Flammability	94V-0
Gender	Receptacle
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	3.037/g
Number of Rows	4
Orientation	Vertical
Packaging Type	Tray
Panel Mount	No
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
PC Tail Length	1.37mm
Pitch - Mating Interface	0.75mm
Plating min - Mating	0.760µm
Plating min - Termination	0.760µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-40° to +80°C

Termination Interface Style	Through Hole - Compliant Pin
-----------------------------	------------------------------

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
Internal iPass+ HD-to-iPass+ HD, 4X Short Body Cable Assemblies	<u>100171</u>
Internal iPass+ HD-to-iPass+ HD, 8X Short Body Cable Assemblies	<u>100172</u>
Internal iPass+ HD-to-iPass+ HD, 4X Short Body Cable Assemblies	<u>100189</u>
Internal iPass+ HD-to-iPass+ HD, 8X Short Body Cable Assemblies	<u>100190</u>
Internal iPass+ HD-to-iPass+ HD, 4X Short Body Cable Assemblies	<u>100219</u>
Internal iPass+ HD-to-iPass+ HD, 8X Short Body Cable Assemblies	<u>100220</u>
Internal iPass+ HD-to-iPass+ HD, 4X Short Body Cable Assemblies	<u>100221</u>
Internal iPass+ HD-to-iPass+ HD, 4X Short Body Cable Assemblies	<u>100222</u>
Internal iPass+ HD-to-iPass+ HD, 4X Short Body Cable Assemblies	<u>100223</u>
Internal iPass+ HD-to-iPass+ HD, 8X Short Body Cable Assemblies	<u>100224</u>
Internal iPass+ HD-to-iPass+ HD, 8X Short Body Cable Assemblies	<u>100225</u>
Internal iPass+ HD-to-iPass+ HD, 8X Short Body Cable Assemblies	<u>100226</u>

Application Tooling