



Part Number : [1722537123](#)
Product Description : Ultra-Fit Tangless Crimp
Terminal, Female, Tin (Sn) Plating, 22-20 AWG
Series Number : 172253
Status : Active
Product Category : Crimp Terminals



Documents & Resources

Drawings

- [1722537123_sd.pdf](#)
- [1722535102-000.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Specifications

- [1723230003-000.pdf](#)
- [1723230001-TS-000.pdf](#)
- [1723231000-PS-CH-000.pdf](#)
- [1723231000-PS-ES-000.pdf](#)
- [1723231000-PS-JP-000.pdf](#)
- [1723231000-PS-SK-000.pdf](#)
- [PS-172323-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC

	(25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	172253
Description	Ultra-Fit Tangless Crimp Terminal, Female, Tin (Sn) Plating, 22-20 AWG
Application	Power, Wire-to-Board
Comments	See Product Specification for maximum current rating by circuit size and wire AWG
Product Name	Ultra-Fit
UPC	191128803540

Electrical

Current - Maximum per Contact	11.5A
Voltage - Maximum	600V AC (RMS)/DC

Physical

Durability (mating cycles max)	25
Gender	Female
Material - Metal	High Conductivity Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.154/g
Packaging Type	Reel
Plating min - Mating	1.524µm
Plating min - Termination	1.524µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.30-1.50mm
Wire Size (AWG)	20, 22
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Ultra-Fit Tangless Single Row Receptacle Housings	<u>172256</u>
Ultra-Fit Tangless Dual Row Receptacle Housings	<u>172258</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for Ultra-Fit Tangless Crimp Terminals, 18-16 AWG (UL1061 Wires)	<u>638248700</u>
FineAdjust Applicator for Ultra-Fit Tangless Crimp Terminals, 22-20 AWG(UL 1061) Wires	<u>639043400</u>
Hand Crimp Tool for Ultra-Fit Tangless Male and Female Terminals, 22-20 AWG (UL 1061)	<u>2238630900</u>

Wire	
------	--

Japan

Description	Part Number
S-1 Applicator for Ultra-Fit Crimp Terminals, 22-20 AWG, UL 1061 Wire	<u>2051563710</u>