



Part Number : [1727040199](#)
Product Description : FCT Plastic Backshell for D-Sub Connector, Shielded, Shell Size 5, Straight Cable Outlet, IP67 Waterproof, with #4-40 Locking Screws, Individual Packing
Series Number : 172704
Status : Active
Product Category : D-Sub Backshells
Engineering Number : FWA5GAE



Documents & Resources

Drawings

- [1727040199_sd.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Backshells
Series	172704
Description	FCT Plastic Backshell for D-Sub Connector, Shielded, Shell Size 5, Straight Cable Outlet, IP67 Waterproof, with #4-40 Locking Screws, Individual Packing
IP Rating	IP67
Magnetic	Yes
Product Name	FCT Products
Type	Plastic
UPC	889056062756

Electrical

Shielded	Yes
Shield Type	Shielded Plastic

Physical

Cable Diameter	9.00-11.00mm
Material - Backshell	PC+ABS
Material - Screw	Brass
Material - Seal	Elastomer
Mounting Style	Locking Screw
Net Weight	47.100/g

Orientation	Straight
Packaging Type	Bag
Plating - Backshell	Nickel
Temperature Range - Operating	-25° to +70°C
Thread Size	4-40 UNC
Thread Type	Standard
Tightening Test Torque	40 Ncm
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	FCT D-Sub, Size 5