



Part Number : [1729532201](#)
Product Description : Micro-Fit Terminal Position Assurance (TPA) Retainer, 22 Circuits, 3.00mm Pitch, UL 94V-0, Low-Halogen, Natural
Series Number : 172953
Status : Active
Product Category : Connector Accessories



Documents & Resources

Drawings

- [1729532201_sd.pdf](#)
- [1729530001-PK-000.pdf](#)

3D Models and Design Files

- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Specifications

- [430450001-PS-KO-000.pdf](#)
- [430450001-PS-SP-000.pdf](#)
- [PS-43045-001.pdf](#)
- [430450007-TS-000.pdf](#)
- [TS-43045-001-001.pdf](#)
- [TS-43045-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC

	(21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	172953
Description	Micro-Fit Terminal Position Assurance (TPA) Retainer, 22 Circuits, 3.00mm Pitch, UL 94V-0, Low-Halogen, Natural
Comments	See Product Specification for maximum current rating by circuit size and wire AWG
Component Type	Terminal Position Assurance
Product Name	Micro-Fit TPA
UPC	889056430203

Physical

Circuits (Loaded)	22
Circuits (maximum)	22
Color - Resin	Natural

Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.241/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Use with Part(s)

Description	Part Number
Micro-Fit TPA Receptacle Housings	<u>172952</u>
Micro-Fit TPA Dual Row Plug Housings	<u>203632</u>