





COMMENT:
 ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
 THIS DRAWING MAY NOT BE REPRODUCED, COPIED, STORED IN A RETRIEVAL SYSTEM,
 AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.



No.	St.	Part	Type Description/Material	Surface plating/Colour/Class
3	22	Signal contact	S0 / Brass	0,8µm Au / AWG 20
2	1	Shell	Steel	tin plated
1	1	Insulator	PBTIP (-55°C - +130°C)	green

		Measurement without tolerance acc. to ISO 2768-m SCALE 2:1		TITLE	
		DATE		NAME	
		DRAWN 15-09-2003		Denzinger	
		CHECKED 16-09-2003		aschlekofer	
		 www.fctgroup.com		DWG.NO.	
				FM25W3S-K121	
1					REV. 1
REV.	DATE	CH.-NO.	ORIGINAL: DIN A3-DRAWING AS A FILE	REPLACEMENT FOR:	F25W3S-K121 a PAGES 1

D-Sub Mixed-Layout Connector

FM25W3S-K121