





RoHS compliant



2	1	Shell	Steel	tin plated
1	1	Insulator	PBT (-55°C to +130°C) acc. UL94V-0	black
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class

FUNCTIONAL SYMBOLS  = 0  = 0  = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
	DIMENSION UNITS		SCALE		MEASUREMENTS WITHOUT TOLERANCE ACC. TO ISO 2768-mK					molex FCT D-Sub Mixed-Layout Connector							
	mm		2:1														
					CURRENT REVISION					FCT D-Sub Mixed-Layout Connector							
					DRWN: DRAWN BY mteubel 15-01-2024												
					APPR: APPR BY msteinbrueck 24-01-2024												
	2		24130		INITIAL REVISION					PRODUCT CUSTOMER DRAWING							
	1				DRWN: DRAWN BY Birgit.Rinder 08-06-2011 APPR: APPR BY sshref 08-06-2011					MATERIAL NUMBER					REVISION		
REV.		CH.-NO.		1731070242													
REPLACEMENT FOR:				FRIST ANGLE PROJECTION			DRAWING			DOCUMENT NUMBER					CUSTOMER		S
							A3-SIZE			F2W2P-K120					GENERAL MARKET		1

COMMENT: _____