



Part Number : [1731070243](#)
Product Description : FCT Mixed Layout D-Sub
Housing, Female, Tin-plated Shell, 2 Circuits Unloaded,
Black Insulator
Series Number : 173107
Status : Active
Product Category : D-Sub Connectors
Engineering Number : F2W2S-K121



Documents & Resources

Drawings

[1731070243 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Connectors
Series	173107
Description	FCT Mixed Layout D-Sub Housing, Female, Tin-plated Shell, 2 Circuits Unloaded, Black Insulator
Magnetic	Yes
Product Name	FCT Products
Type	Mixed Layout
UPC	889056745215

Electrical

Shielded	Yes
----------	-----

Physical

Circuits (Loaded)	0
Circuits (maximum)	2
Color - Resin	Black
Gender	Female
Material - Resin	PBT
Material - Shell	Steel
Net Weight	4.600/g
Number of Rows	1
Packaging Type	Carton
Panel Mount	Front or Rear

Panel Mount Method	Flange
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	2.84mm
Pitch - Termination Interface	2.54mm
Plating - Shell	Tin
Polarized to Mating Part	Yes
Polarized to PCB	No
Ports	1
Temperature Range - Operating	-55° to +130°C
Waterproof / Dustproof	No

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	FCT Mixed Layout D-Sub, Size 1, 2W2, Plug

Use with Part(s)

Description	Part Number
Use With	FCT Coaxial, High Power, High Voltage, or Pneumatic Contacts