



Part Number : [1731070468](#)

Product Description : FCT Mixed Layout D-Sub Connector, Female, Straight, PCB Through Hole, Gold Plating, Tin-plated Shell, 6.60mm Snap-in Bolt, Female Screw Locks and Washers, 9 Circuits Loaded (4 High Power, 5 Signal), Green Insulator

Series Number : 173107

Status : Active

Product Category : D-Sub Connectors

Engineering Part Number : FM9W4S1-2519



Documents and Resources

Drawings

[1731070468 sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant with Exemption 6(c); 6(a)-I per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Connectors
Series	173107
Description	FCT Mixed Layout D-Sub Connector, Female, Straight, PCB Through Hole, Gold Plating, Tin-plated Shell, 6.60mm Snap-in Bolt, Female Screw Locks and Washers, 9 Circuits Loaded (4 High Power, 5 Signal), Green Insulator
IP Rating	IP20
Magnetic	Yes
Product Name	FCT Products
Type	Mixed Layout
UPC	191128236843

Electrical

Current - Maximum per Contact	7.5A, 20.0A
Shielded	Yes

Physical

Circuits (Loaded)	9
Circuits (maximum)	9

Color - Resin	Green
Durability (mating cycles min)	200
Gender	Female
Material - Contact	Copper Alloy
Material - Resin	PBT
Material - Shell	Steel
Net Weight	18.100/g
Number of Rows	2
Orientation	Straight
Packaging Type	Carton
Panel Mount	Rear
Panel Mount Method	Thread-In
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
PC Tail Length	10.30mm
Pitch - Mating Interface	2.84mm
Pitch - Termination Interface	2.54mm
Plating - Contact	Gold over Nickel Gold/Tin over Nickel
Plating min - Mating	0.100µm, 0.200µm
Plating min - Termination	0.100µm, 5.000µm
Plating - Shell	Tin
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-55° to +130°C
Termination Style	Through Hole
Waterproof / Dustproof	No
Waterproof / Dustproof Type	IP20

Mates With / Use With

Mates with Part(s)

Description	Part Number
-------------	-------------

Mates With	FCT Mixed Layout D-Sub, Size 3, 9W4, Plug
------------	--

This document was generated on Feb 27, 2026