Part Number : 1731120206
Product Description : FCT Machined Contact, Male, Crimp, 0.20µm Gold Plating, 28-26 AWG, 500 Pieces
Series Number : 173112
Status : Active
Product Category : D-Sub Contacts
Engineering Number : FK20P26-02V-5783



Documents & Resources

Drawings

1731120206_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

1731120004-PK-000.pdf

2195600650-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Contacts
Series	173112
Description	FCT Machined Contact, Male, Crimp, 0.20µm Gold Plating, 28-26 AWG, 500 Pieces
Contact Type	Machined Crimp
Magnetic	Yes
Product Name	FCT Products
Type	Standard Density
UPC	889056489614

Electrical

Current - Maximum per Contact	7.5A

Physical

Durability (mating cycles min)	200
Gender	Male
Material - Contact	Brass
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Gold over Nickel
Net Weight	0.200/g
Orientation	Straight

Packaging Type	Bag
Plating min - Mating	0.200µm
Plating min - Termination	0.200µm
Temperature Range - Operating	-55° to +130°C
Termination Style	Crimp
Wire Size (AWG)	26, 28

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	FCT Standard-Density Connectors

Application Tooling

Global

Description	Part Number
FCT Hand Crimp Tool, Mini Frame, 8-Step Adjust	1731121730
FCT Locator for Size 20 Contacts, Plug and Socket	1731121733
FCT Installation and Removal Tool for D-Subs	1731121744
