



Part Number : [1731130155](#)
Product Description : FCT High-Density D-Sub Connector, Male, Right-Angle, PCB Through Hole, 0.80µm Gold Plating, with Machined Contacts and Metal Bracket, 44 Circuits
Series Number : 173113
Status : Active
Product Category : D-Sub Connectors
Engineering Part Number : F25-44P135G0-5979



Documents and Resources

Drawings

[1731130155_sd.pdf](#)
[Symbol and Footprint \(Multi-Format\)](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Connectors
Series	173113
Description	FCT High-Density D-Sub Connector, Male, Right-Angle, PCB Through Hole, 0.80µm Gold Plating, with Machined Contacts and Metal Bracket, 44 Circuits
IP Rating	IP20
Magnetic	Yes
Product Name	FCT Products
Type	High Density
UPC	191128142625

Electrical

Current - Maximum per Contact	5.0A
Shielded	Yes

Physical

Circuits (Loaded)	44
Circuits (maximum)	44
Color - Resin	Black
Gender	Male
Material - Contact	Copper Alloy
Material - Resin	PBT
Material - Shell	Steel
Net Weight	16.800/g

Number of Rows	3
Orientation	Right-Angle
Packaging Type	Carton
Panel Mount	Rear
Panel Mount Method	Flange
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
PC Tail Length	7.98mm
Pitch - Mating Interface	1.98mm
Pitch - Termination Interface	1.98mm
Plating - Contact	Gold over Nickel
Plating min - Mating	0.800µm
Plating min - Termination	0.800µm
Plating - Shell	Tin
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-55° to +130°C
Termination Style	Through Hole
Waterproof / Dustproof	No
Waterproof / Dustproof Type	IP20

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	FCT High-Density D-Sub, Size 3, 44 Position, Socket