



Part Number : [190690112](#)
Product Description : Krimptite Ring Tongue
Terminal for 16-14 AWG Wire
Series Number : 19069
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : BB-137-06



Documents & Resources

Drawings
[190690112 sd.pdf](#)

3D Models and Design Files
[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications
[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

- Compliance Statements
- EU RoHS
 - REACH SVHC
 - Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19069
Description	Krimptite Ring Tongue Terminal for 16-14 AWG Wire
Keyword	Ring Terminal, Ring Terminals
Product Name	Krimptite
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800755066883

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.678/g
Packaging Type	Bag
Plating min - Mating	2.540µm

Plating min - Termination	2.540µm
Stud Size	5-6 (M3-3.5)
Termination Interface Style	Crimp or Compression
Wire Size (AWG)	14, 16
Wire Size mm ²	1.30-2.00

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm ² - 0.5mm ²	<u>640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>640160038</u>