



Part Number : [191640315](#)

Product Description : Perma-Seal Male Snap Plug for 16-14 AWG Wire, Diameter 3.96mm, Mylar Tape Carrier

Series Number : 19164

Status : Active

Product Category : Quick Disconnects

Engineering Part Number : SB-289T



Documents & Resources

Drawings

[191640315 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2020)4578-DC (25 June 2020)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19164
Description	Perma-Seal Male Snap Plug for 16-14 AWG Wire, Diameter 3.96mm, Mylar Tape Carrier
Product Name	Perma-Seal
Type	Snap Plug
UPC	800753115705

Agency

UL	E152602
----	---------

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Blue
Gender	Male
Glow-Wire Capable	No
Insulated	Partial
Insulation	NiAc

Lock to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.455/g
Orientation	Straight
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Tab Thickness	N/A
Tab Width	N/A
Temperature Range - Operating	-55° to +125°C
Wire Insulation Diameter	6.71mm max.
Wire Size (AWG)	14, 16

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>192880267</u>