



Part Number : [2000960201](#)
Product Description : TAK50 Receptacle Terminal,
Unsealed, S-Grip, D-Wind, Left Reel Payoff
Series Number : 200096
Status : Obsolete
Product Category : Crimp Terminals



Documents and Resources

Specifications

[2000960001-AS-CH-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Duty-To-Declare
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
Category	Crimp Terminals
Series	200096
Description	TAK50 Receptacle Terminal, Unsealed, S-Grip, D-Wind, Left Reel Payoff
Application	Automotive, Signal, Wire-to-Board
Comments	Stainless Steel Hood/Sleeve
Product Name	TAK50
UPC	191128074735

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	14V DC

Physical

Durability (mating cycles max)	10
Gender	Female
Grip Code	S
Material - Metal	Copper Alloy, Stainless Steel
Material - Plating Mating	Tin
Net Weight	0.055/g
Packaging Type	Reel
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	0.95-1.05mm
Wire Size (AWG)	N/A
Wire Size mm ²	0.13

Mates With / Use With

Use with Part(s)

Description	Part Number
-------------	-------------

stAK50h Hybrid Receptacles	<u>160014</u>
----------------------------	---------------

Application Tooling

Global

Description	Part Number
Extraction Tool for stAK50h Crimp Terminals	<u>2002221600</u>

This document was generated on Dec 08, 2025

Obsolete