



Part Number : [2033879200](#)

Product Description : Open19 Foundation (6)
zQSFP+-to-(12) Impel 92 Ohm 4-by-2 Male Breakout
Cable Assembly, Twinax Cable, 30 AWG, 761.00mm
Length

Series Number : 203387

Status : Active

Product Category : High-Speed I/O Cable
Assemblies



Documents & Resources

Drawings

[2033879200 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per ED/88/2018 (15 January 2019)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	High-Speed I/O Cable Assemblies
Series	203387
Description	Open19 Foundation (6) zQSFP+-to-(12) Impel 92 Ohm 4-by-2 Male Breakout Cable Assembly, Twinax Cable, 30 AWG, 761.00mm Length
Assembly Configuration	Dual Ended Connectors
Connector to Connector	6 QSFP28-to-12 Impel, 6 zQSFP+-to-12 Impel
Product Name	Impel,zQSFP Plus,zQSFP+
Type	Pluggable
UPC	193264054886

Electrical

Current - Maximum per Contact	0.75A
Data Rate	28.0 Gbps
Impedance	92Ω
Voltage - Maximum	29.9V AC (RMS)/DC

Physical

Cable Bundling	None
Cable Length	761.00mm
Circuits (Loaded)	96 TO 96
Color - Resin	Black
Gender	Male-Male
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold

Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.000/g
Packaging Type	Tray
Plating min - Mating	0.762μm
Release Style	Pull Tab
Single Ended	No
Wire/Cable Type	Twinax
Wire Size (AWG)	30

Mates With / Use With

Mates with Part(s)

Description	Part Number
Impel 90 Ohm, 4 Pair Right-Angle Daughtercard, 1.90mm Pitch, Unguided, 12 Columns, 96 Circuits, Plated Through Hole Dimension 0.36mm	<u>1713201022</u>
Impel 90 Ohm, 4 Pair Right-Angle Daughtercard, 1.90mm Pitch, Right Guided, 2 Columns, 16 Circuits, Plated Through Hole Dimension 0.36mm	<u>1713209032</u>