




Part Number : [2093111115](#)
Product Description : Mirror Mezz Hermaphroditic Connector, 2.50mm Connector Height, BGA-Attach Mounting, 15 Pair, 11 Row, 688 Circuits, 0.76µm Gold (Au) Plating, with Pegs
Series Number : 209311
Status : Active
Product Category : Board-to-Board Connectors



Documents & Resources

Drawings

- [2093111115 sd.pdf](#)
- [2093118500-000.pdf](#)

3D Models and Design Files

- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)
- [2093111115 dxf.dxf](#)
- [2093111115EE-000.pdf](#)
- [2093111115SP-000.zip](#)

Specifications

- [2028280001-AS-000.pdf](#)
- [2028289005PS-001.pdf](#)
- [2093110001-AS-000.pdf](#)
- [2028280001-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant

Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	209311
Description	Mirror Mezz Hermaphroditic Connector, 2.50mm Connector Height, BGA-Attach Mounting, 15 Pair, 11 Row, 688 Circuits, 0.76µm Gold (Au) Plating, with Pegs
Application	Board-to-Board, Mezzanine
Component Type	PCB Header
Product Name	Mirror Mezz
UPC	191130509140

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	0.75A (1 Oz Cu Trace), 1.2A (2 Oz Cu Trace)
Voltage - Maximum	30V AC (RMS)/DC

Physical

Breakaway	No
Circuits (Loaded)	688
Circuits (maximum)	688
Color - Resin	Black
Durability (mating cycles max)	100
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	None
Mated Height	5.00mm
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	5.360/g
Number of Rows	11
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Retention	Yes
Pitch - Mating Interface	1.50mm, 4.00mm
Plating min - Mating	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	Yes
Temperature Range - Operating	-55° to +105°C

Termination Interface Style	BGA Solder
-----------------------------	------------

Solder Process Data

Max-Duration	20
Lead-Free Process Capability	REFLOW
Max-Cycle	1
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mirror Mezz Hermaphroditic Connectors	<u>209311</u>
Mates With	This is a hermaphroditic, self-mating part.