



Part Number : [2174711211](#)
Product Description : Pre-Crimped Lead Ultra-Fit
Female-to-Pigtail, Gold (Au) Plating, 75.00mm Length,
18 AWG, Black
Series Number : 217471
Status : Active
Product Category : Power and Signal Cable
Assemblies



Documents & Resources

Drawings
[2174711211 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	217471
Description	Pre-Crimped Lead Ultra-Fit Female-to-Pigtail, Gold (Au) Plating, 75.00mm Length, 18 AWG, Black
Application	Power, Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Ultra-Fit Crimp Terminals
Keyword	Pre-Crimped Leads
Product Name	Ultra-Fit
UPC	195842069909

Electrical

Current - Maximum per Contact	12.0A
Voltage - Maximum	600V AC (RMS)/DC

Physical

Cable Length	75.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Pigtail
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold
Net Weight	0.945/g
Packaging Type	Bag
Single Ended	Yes
Termination Interface Style	Crimp or Compression

Wire/Cable Type	UL 1061
Wire Size (AWG)	18