



Part Number : [2174712225](#)
Product Description : Pre-Crimped Lead Ultra-Fit
Female-to-Pigtail, Gold (Au) Plating, 450.00mm Length,
16 AWG, Red
Series Number : 217471
Status : Active
Product Category : Power and Signal Cable
Assemblies



Documents & Resources

Drawings
[2174712225 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	217471
Description	Pre-Crimped Lead Ultra-Fit Female-to-Pigtail, Gold (Au) Plating, 450.00mm Length, 16 AWG, Red
Application	Power, Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Ultra-Fit Crimp Terminals
Keyword	Pre-Crimped Leads
Product Name	Ultra-Fit
UPC	195842070295

Electrical

Current - Maximum per Contact	12.0A
Voltage - Maximum	600V AC (RMS)/DC

Physical

Cable Length	450.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Red
Gender	Female-Pigtail
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold
Net Weight	6.794/g
Packaging Type	Bag
Single Ended	Yes
Termination Interface Style	Crimp or Compression

Wire/Cable Type	UL 1061
Wire Size (AWG)	16

This document was generated on Sep 24, 2025